

# CARSON®

# DS-50GL

## HandHeld

### 3x Magnifier with 6x Spot Lens

Congratulations on selecting your new magnifier! In order to achieve optimum performance, please follow instructions for proper use and care.



#### PRODUCT SPECIFICATION

Magnification:	3x / 6x Spot Lens
Weight:	0.05 lbs
Dimensions:	2.2" x 0.4" x 5.3"

#### USING THE MAGNIFIER

Place magnifier over the subject you are viewing.

**For Best Results:**

- Depending on your vision, you may need to move the magnifier closer or further away until focused.

#### USING THE SPOT LENS

To see superfine details, use the spot lens.

**For Best Results:**

- The magnifier should be close to the subject when using the spot lens.

#### CARE

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

**Customer Service:**

If you experience any difficulties, please contact us and we will be happy to help you.



✉ info@carson.com



✉ uksupport@carson.com



✉ eusupport@carson.com

For warranty information, visit [www.carson.com/warrant](http://www.carson.com/warrant)

**www.carson.com**

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000