

### 3x Stand Loupe with 12x Focusing Loupe

Congratulations on selecting your new DualView™! In order to achieve optimum performance, please follow instructions for proper use and care.


#### PRODUCT SPECIFICATIONS

Magnification:	3x Stand Loupe / 12x Focusing Loupe
Weight:	0.15 lbs
Dimensions:	4.0" x 2.0" x 1.6"




#### USING 3X STAND LOUPE

1. Place loupe over subject you are viewing.
2. Start with loupe flat against a table. Depending on your vision, raise as needed to focus.



#### USING 12X FOCUSING LOUPE

1. Place loupe over viewing subject.
2. Your eye(s) should be reasonably close to loupe.
3. Adjust Focusing Ring until subject is sharp and clear.



#### CLEANING

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

#### Customer Service:

If you experience any difficulties, please contact us and we will be happy to help you.



✉ info@carson.com



✉ uksupport@carson.com



✉ eusupport@carson.com

For warranty information, visit [www.carson.com/warranty](http://www.carson.com/warranty)

**www.carson.com**

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000