

CARSON®

LumiLoupe™

7x Stand Magnifier



LL-77

Congratulations on selecting your new LumiLoupe Stand Magnifier! In order to achieve optimum performance, please follow instructions for proper use and care.

PRODUCT SPECIFICATION:

Magnification:	7x
Weight:	0.26 lbs
Dimensions:	3.0" x 3.0" x 2.5"

USING LOUPE:

1. Place loupe over viewing object.
2. Your eye(s) should be reasonably close to loupe.
3. It's best to start with loupe flat against a table and raise as needed to focus.

CARE:

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

Customer Service:

If you experience any difficulties, please contact us and we will be happy to help you.



✉ info@carson.com



✉ uksupport@carson.com



✉ eusupport@carson.com

For warranty information, visit www.carson.com/warranty

www.carson.com

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000